
LUTRON | Triathlon Shades Selection Guide



Are BELLITHON

Please note: Product options may vary depending on application and intended use. For more technical information, reference **www.lutron.com** or work with your qualified Lutron provider. Product availability is subject to change.

LUTRON | Triathlon Shades Selection Guide

Step 3 Select Control

Pico remote (standalone)	Caséta system	RadioRA 3 system	HomeWorks system

Step 4 Select Shade Mount and Measurements (choose one)

Inside Mount Enter window measu	rements below. It	f full-recess is des	ired. check the proj	ection dimension o	f vour shade type.
Width*:			Height:		<u> </u>
→ A →	A ir	ı/mm		D	_ in/mm
←B	B ir	ı/mm	D E F	E	_ in/mm
C	C ir	n/mm		F	_ in/mm
Smallest width	n: ir	ı/mm	Smallest	height:	_ in/mm
Outside Mount Enter width and heig	jht below.				
On Trim	Above ⁻	Frim ** (includes s	pacers to clear trim	up to ½ in (13 mn	n) thick)
Width*: Enter the	e width of the are	ea you want the f	abric to cover		_ in/mm
Height: Enter the	e distance from t	the top of the hea	adrail to the window	sill	in/mm
Vhen mounting above trim, th roller) above the top edge of t		must be at least 31/8	in (80 mm) (Standard an	d Architectural honeyc	omb), or 4½ in (114 mm)
Maximum width for a Standard Ind WIDR roller shade is 144 i	d or Architectural ho	neycomb shade is 96) in (2,438 mm). Maximu	m width for a roller sha	ade is 108 in (2,743 mm)
loneycomb shade pr	ojection: full-re	cess depth for i	nside mount		
Battery powered ap 'n' Tilt brackets	2½ in (64 mm)		Manual shade Stationary brackets	2 in (51 mm)	

LUTRON | Triathlon Shades Selection Guide

Without Fascia*			Fabric-Wrapped	Architectural
battery powered	wired power	cordless manual	Fascia	Fascia
3 in (76 mm)	3 in (76 mm)	3 in (76 mm)	3¾ in (86 mm)	<u>3% in</u> (86 mm)

* Without fascia, the projection varies with the size of the fabric roll-up (fabric panel height). The dimension shown is based on the largest available fabric panel height; the maximum projection.

Step 5 Select Fabric

Utilize your fabric binders or visit <u>www.lutron.com/fabrics</u> Fabric P/N:

Optional Enhancements for Honeycomb Shade



For more information, please visit www.lutron.com or call 1.800.446.1503

The Lutron logo, Lutron, Caséta, HomeWorks, Pico, RadioRA 3, and Triathlon are trademarks or registered trademarks of Lutron Electronics Co., Inc., in the U.S. and other countries.

www.lutron.com

World Headquarters: 1.610.282.3800 | 24/7 Technical Support: 1.800.523.9466 | Customer Service: 1.888.LUTRON1 (1.888.588.7661) © 12/2023 Lutron Electronics Co., Inc. | P/N 368-4408 REV C